





LIMTECH Alliance and HEMCP

# B4: Phase changes in liquid metals for direct energy conversion.

# Alkali Metal Thermo-Electric Converter (AMTEC)

N. Diez de los Rios Ramos, M. Bologa, A. Onea, W. Hering, R. Stieglitz

(Na) Na(0) sodium atoms

#### Alkali Metal Thermo-Electric Converter (AMTEC)

- Direct conversion of heat to electricity
- Working fluid/vapor: sodium


Na → Na+ + e<sup>-</sup>


External Load

Key process: (Δp across BASE)

High expected efficiency (~ 40 %)









Operation principle of AMTEC

#### Electrode sputter layer analysis

- SEM analysis ✓ Porous structure
  - (TiC)
- Partial detachment of sputter layer
- EDS analysis (TiC)
- ✓ Confirmed TiC layer
- ✓ Na diffusion through the electrode
- Two phases in the ceramic



- 4-Point Probe. Sheet resistance measurements\*
  - $\checkmark$  ρ(TiN)=0.18 0.7 Ω/sq, ρ(TiC)=22.6 54.8 Ω/sq
  - Measured ρ lower than in the literature
  - Not homogeneous resistance
     (detached areas)
     \* Smits, Bell. Sys. Tech. J. (1957)



## Summary


The aim of the work was to develop a layout and engineering solutions for the construction and set into operation of the ATEFA and AMTEC test cell by using available technologies within the Helmholtz AMTEC center (HAC) and based on the experiences in liquid metal technology in the Helmholtz Alliance LIMTECH. First step was to regain the

know-how in the AMTEC technology based on the work started at KIT in the nineties. The main challenges of the work regarding the construction of the AMTEC test cell were the development of i) a porous cathode coating of the BASE, ii) a high temperature resistant ceramic-metal joint, iii) a fully electrically isolated cell design, iv) a fully instrumented cell considering the reduced space of the cell structure, the corrosive medium (Na) and the high operating temperature. Moreover a data acquisition and control system were defined and the experimental procedure was developed taking into consideration handling solutions for high-temperature liquid sodium.

ATEFA has been set into operation and short term tests have been successfully performed up to 700 °C. The proof of concept of the AMTEC technology has been achieved and the cell behavior was analyzed at different temperature and pressure conditions. The evaluation of results are in good agreement with the literature.

#### **AMTEC TEst FAcility (ATEFA), status**

- ✓ Integration of AMTEC test module finished
- ✓ Construction of ATEFA finished
- ✓ Data acquisition and control system finished and tested
- ✓ Ceramic -metal joint tested (700 °C)
- Ceramic coating experimentally analyzed (SEM, EDS,4-point probe)
- ✓ ATEFA successfully tested (700 °C)
   → pressure and heating/cooling tests
- Measurement campaign finished
- AMTEC proof of concept achieved
- Evaluation of results finished



Ni-sealing
ß"-Alumina


Ceramic-metal joint

Niobium

Current collector



AMTEC Test cell




ATEFA


### **AMTEC** experimental results

Cell temp. distribution

Open circuit voltage (OCV) vs. Nernst voltage



Cell power in terms of temperature



- Summary and conclusions
  - Cell power measured at 500 700 °C
  - Large influence of the ceramic wetting (<350 °C) on OCV
  - Quantitative good agreement of OCV with literature
  - Qualitative good agreement of IV curve with literature
  - Low cell current due to lack of electrode coating
  - Cell power increase with T<sub>B</sub>